


TEC FLEX Low & High Power Protect

Moduli LED per applicazioni semi-professionali



Caratteristiche prodotto

- Striscia LED flessibile e tagliabile
- Available with color temperature: 2,700K, 3,000 K, 4,000 K
- Up to 50,000 hrs lifetime @ tc max
- Color consistency in 3 SDCM

Vantaggi prodotto

- Facile installazione su molte superfici lisce grazie al nastro autoadesivo sul lato posteriore



Scheda della famiglia di prodotto

Dati tecnici

Dati elettrici

Descrizione del prodotto	Tensione nominale	Tipo di corrente	Potenza di costruzione	Gamma di tensione	Accidental reverse input voltage protection up to
TFP300-G1 -827-05	240 V	DC	1400 W	23...25 V	25 V
TFP300-G1 -830-05	240 V	DC	1400 W	23...25 V	25 V
TFP300-G1 -840-05	240 V	DC	1400 W	23...25 V	25 V
TFP300-G1 -865-05	240 V	DC	1400 W	23...25 V	25 V
TFP300-G1 -850-05	240 V	DC	1400 W	23...25 V	25 V
TFP1000-G1 -827-05	240 V	DC	4750 W	23...25 V	25 V
TFP1000-G1 -830-05	240 V	DC	4750 W	23...25 V	25 V
TFP1000-G1 -840-05	240 V	DC	4750 W	23...25 V	25 V
TFP1000-G1 -865-05	240 V	DC	4750 W	23...25 V	25 V
TFP1000-G1 -850-05	240 V	DC	4750 W	23...25 V	25 V
TFP2000-G1 -827-05	240 V	DC	7750 W	23...25 V	25 V
TFP2000-G1 -830-05	240 V	DC	7750 W	23...25 V	25 V
TFP2000-G1 -840-05	240 V	DC	7750 W	23...25 V	25 V
TFP2000-G1 -865-05	240 V	DC	7750 W	23...25 V	25 V
TFP2000-G1 -850-05	240 V	DC	7750 W	23...25 V	25 V

Dati fotometrici

Descrizione del prodotto	Tonalità di luce del LED	Indice di resa cromatica Ra	Colore della luce (descrizione)
TFP300-G1 -827-05	bianco	80	Bianco
TFP300-G1 -830-05	bianco	80	Bianco
TFP300-G1 -840-05	bianco	80	Bianco
TFP300-G1 -865-05	bianco	80	Bianco
TFP300-G1 -850-05	bianco	80	Bianco
TFP1000-G1 -827-05	bianco	80	Bianco
TFP1000-G1 -830-05	bianco	80	Bianco
TFP1000-G1 -840-05	bianco	80	Bianco
TFP1000-G1 -865-05	bianco	80	Bianco
TFP1000-G1 -850-05	bianco	80	Bianco
TFP2000-G1 -827-05	bianco	80	Bianco
TFP2000-G1 -830-05	bianco	80	Bianco
TFP2000-G1 -840-05	bianco	80	Bianco
TFP2000-G1 -865-05	bianco	80	Bianco
TFP2000-G1 -850-05	bianco	80	Bianco

Scheda della famiglia di prodotto

Dimensioni e peso

Descrizione del prodotto	Lunghezza	Peso prodotto
TFP300-G1 -827-05	50000 mm	26900 g
TFP300-G1 -830-05	50000 mm	26900 g
TFP300-G1 -840-05	50000 mm	26900 g
TFP300-G1 -865-05	50000 mm	26900 g
TFP300-G1 -850-05	50000 mm	26900 g
TFP1000-G1 -827-05	50000 mm	26900 g
TFP1000-G1 -830-05	50000 mm	26900 g
TFP1000-G1 -840-05	50000 mm	26900 g
TFP1000-G1 -865-05	50000 mm	26900 g
TFP1000-G1 -850-05	50000 mm	26900 g
TFP2000-G1 -827-05	50000 mm	27300 g
TFP2000-G1 -830-05	50000 mm	27300 g
TFP2000-G1 -840-05	50000 mm	27300 g
TFP2000-G1 -865-05	50000 mm	27300 g
TFP2000-G1 -850-05	50000 mm	27300 g

Temperature e condizioni di utilizzo

Descrizione del prodotto	Temperatura di funzionamento	Temperatura di stoccaggio
TFP300-G1 -827-05	-25...80 °C	-30...85 °C
TFP300-G1 -830-05	-25...80 °C	-30...85 °C
TFP300-G1 -840-05	-25...80 °C	-30...85 °C
TFP300-G1 -865-05	-25...80 °C	-30...85 °C
TFP300-G1 -850-05	-25...80 °C	-30...85 °C
TFP1000-G1 -827-05	-25...80 °C	-30...85 °C
TFP1000-G1 -830-05	-25...80 °C	-30...85 °C
TFP1000-G1 -840-05	-25...80 °C	-30...85 °C
TFP1000-G1 -865-05	-25...80 °C	-30...85 °C
TFP1000-G1 -850-05	-25...80 °C	-30...85 °C
TFP2000-G1 -827-05	-25...80 °C	-30...85 °C
TFP2000-G1 -830-05	-25...80 °C	-30...85 °C
TFP2000-G1 -840-05	-25...80 °C	-30...85 °C
TFP2000-G1 -865-05	-25...80 °C	-30...85 °C
TFP2000-G1 -850-05	-25...80 °C	-30...85 °C

Scheda della famiglia di prodotto

Dati di prodotto aggiuntivi

Descrizione del prodotto	EAN sostitutivo	ID of contained light source [AGGR]
TFP300-G1 -827-05	4052899528031, 4052899528116	LS_SHZ_600315
TFP300-G1 -830-05	4052899528055, 4052899528130	LS_SHZ_600316
TFP300-G1 -840-05	4052899528079, 4052899528154	LS_SHZ_600317
TFP300-G1 -865-05	4052899528093, 4052899528178	LS_SHZ_600319
TFP300-G1 -850-05		LS_SHZ_600318
TFP1000-G1 -827-05	4052899526211	LS_SHZ_600320
TFP1000-G1 -830-05	4052899526235	LS_SHZ_600321
TFP1000-G1 -840-05	4052899526259	LS_SHZ_600322
TFP1000-G1 -865-05	4052899526273	LS_SHZ_600324
TFP1000-G1 -850-05		LS_SHZ_600323
TFP2000-G1 -827-05	4052899528468	LS_SHZ_600298
TFP2000-G1 -830-05	4052899528482	LS_SHZ_600326
TFP2000-G1 -840-05	4052899528505	LS_SHZ_600327
TFP2000-G1 -865-05	4052899528529	LS_SHZ_600329
TFP2000-G1 -850-05		LS_SHZ_600328

Certificati, Norme, Direttive

Descrizione del prodotto	Norme	Energy efficiency class of the contained light source
TFP300-G1 -827-05	CE/ENEC/EAC	E
TFP300-G1 -830-05	CE/ENEC/EAC	E
TFP300-G1 -840-05	CE/ENEC/EAC	E
TFP300-G1 -865-05	CE/ENEC/EAC	E
TFP300-G1 -850-05	CE/ENEC/EAC	E
TFP1000-G1 -827-05	CE/ENEC/EAC	F
TFP1000-G1 -830-05	CE/ENEC/EAC	E
TFP1000-G1 -840-05	CE/ENEC/EAC	E
TFP1000-G1 -865-05	CE/ENEC/EAC	E
TFP1000-G1 -850-05	CE/ENEC/EAC	E
TFP2000-G1 -827-05	CE/ENEC/EAC	F
TFP2000-G1 -830-05	CE/ENEC/EAC	E
TFP2000-G1 -840-05	CE/ENEC/EAC	E
TFP2000-G1 -865-05	CE/ENEC/EAC	E
TFP2000-G1 -850-05	CE/ENEC/EAC	E

Scheda della famiglia di prodotto

Dati logistici

Descrizione del prodotto	Codice prodotto di base
TFP300-G1 -827-05	85395100000
TFP300-G1 -830-05	85395100000
TFP300-G1 -840-05	85395100000
TFP300-G1 -865-05	85395100000
TFP300-G1 -850-05	85395100000
TFP1000-G1 -827-05	85395100000
TFP1000-G1 -830-05	85395100000
TFP1000-G1 -840-05	85395100000
TFP1000-G1 -865-05	85395100000
TFP1000-G1 -850-05	85395100000
TFP2000-G1 -827-05	85395100000
TFP2000-G1 -830-05	85395100000
TFP2000-G1 -840-05	85395100000
TFP2000-G1 -865-05	85395100000
TFP2000-G1 -850-05	85395100000

Environmental information
Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)

Descrizione del prodotto	Date of Declaration	Primary Article Identifier	Candidate List Substance 1
TFP300-G1 -827-05	07-07-2023	4062172106627	Lead
TFP300-G1 -830-05	07-07-2023	4062172106641	Lead
TFP300-G1 -840-05	11-04-2023	4062172106665	No declarable substances contained
TFP300-G1 -865-05	11-04-2023	4062172106702	No declarable substances contained
TFP300-G1 -850-05	11-04-2023	4062172106689	No declarable substances contained
TFP1000-G1 -827-05	07-07-2023	4062172106726	Lead
TFP1000-G1 -830-05	07-07-2023	4062172106740	Lead
TFP1000-G1 -840-05	07-07-2023	4062172106764	Lead
TFP1000-G1 -865-05	07-07-2023	4062172106801	Lead
TFP1000-G1 -850-05	21-07-2023	4062172106788	Lead
TFP2000-G1 -827-05	07-07-2023	4062172106825	Lead
TFP2000-G1 -830-05	07-07-2023	4062172106849	Lead
TFP2000-G1 -840-05	07-07-2023	4062172106863	Lead
TFP2000-G1 -865-05	07-07-2023	4062172106900	Lead
TFP2000-G1 -850-05	07-07-2023	4062172106887	Lead

Scheda della famiglia di prodotto

Descrizione del prodotto	CAS No. of substance 1	Safe Use Instruction	Declaration No. in SCIP database
TFP300-G1 -827-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	aa00d901-7681-43d3-b39a-799982271c08
TFP300-G1 -830-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	01dbb983-4301-49d5-a5f5-39360f03e065
TFP300-G1 -840-05			No declarable substances contained
TFP300-G1 -865-05			No declarable substances contained
TFP300-G1 -850-05			No declarable substances contained
TFP1000-G1 -827-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	807d90b4-f529-4a4c-8d2b-9714849306c4
TFP1000-G1 -830-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	dd03dde0-7181-412a-a79f-c57297169c50
TFP1000-G1 -840-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	59209483-c933-420b-847f-5325be7af197
TFP1000-G1 -865-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	e037d093-3865-48e6-919d-0f13fc36131f
TFP1000-G1 -850-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	e3a453a2-4f36-4c4f-aa72-374a3c937902
TFP2000-G1 -827-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	ae550d68-6088-4f32-b3a4-eba43f638b02
TFP2000-G1 -830-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	ab29cb42-27c3-4c7b-9860-a11730119d8c
TFP2000-G1 -840-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	b74546d0-fb3b-42f4-8aa8-2cf3bd0b0656
TFP2000-G1 -865-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	b61971db-48c3-417d-98aa-cc744c4926f9

Scheda della famiglia di prodotto

Descrizione del prodotto	CAS No. of substance 1	Safe Use Instruction	Declaration No. in SCIP database
TFP2000-G1 -850-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	0cb3a442-2d96-4be1-a748-7080ad858a93

Apparecchiatura / Accessori

- Connessione più semplice con il sistema opzionale CONNECTsystem

Consigli di applicazione

Per informazioni più dettagliate e grafici consultare la scheda tecnica

Supporto tecnico e di vendita

Supporto tecnico e di vendita www.osram.it

Download dati

File	
	User instruction TEC Flex IP66
	Product Datasheet TEC Flex IP66 Product Datasheet (EN)
	Brochure Light is strong - Discover the versatile and flexible lighting system OSRAM 24V TEC Flex (EN)
	Certificati TFX ENEC 130520
	Dichiarazioni di conformità TECFlex CE 4210017 080823
	Dati CAD DWG TEC Flex and TEC Flex Shortpitch
	Eulumdat EULUMDAT TEC Flex Protect
	Eulumdat TFP300-G1-827 LTD 130122
	IES data TFP300-G1-827 IES 130122
	Eulumdat TFP300-G1-830 LTD 130122
	IES data TFP300-G1-830 IES 130122

Scheda della famiglia di prodotto

	Eulumdat TFP300-G1-840 LTD 130122
	IES data TFP300-G1-840 IES 130122
	Eulumdat TFP300-G1-865 LTD 130122
	IES data TFP300-G1-865 IES 130122
	Eulumdat TFP300-G1-850 LTD 130122
	IES data TFP300-G1-850 IES 130122
	Eulumdat TFP1000-G1-827 LTD 130122
	IES data TFP1000-G1-827 IES 130122
	Eulumdat TFP1000-G1-830 LTD 130122
	IES data TFP1000-G1-830 IES 130122
	Eulumdat TFP1000-G1-840 LTD 130122
	IES data TFP1000-G1-840 IES 130122
	Eulumdat TFP1000-G1-865 LTD 130122
	IES data TFP1000-G1-865 IES 130122
	Eulumdat TFP1000-G1-850 LTD 130122
	IES data TFP1000-G1-850 IES 130122
	Eulumdat TFP2000-G1-827 LTD 130122
	IES data TFP2000-G1-827 IES 130122
	Eulumdat TFP2000-G1-830 LTD 130122
	IES data TFP2000-G1-830 IES 130122
	Eulumdat TFP2000-G1-840 LTD 130122
	IES data TFP2000-G1-840 IES 130122
	Eulumdat TFP2000-G1-865 LTD 130122

Scheda della famiglia di prodotto

	IES data TFP2000-G1-865 IES 130122
	Eulumdat TFP2000-G1-850 LTD 130122
	IES data TFP2000-G1-850 IES 130122

Ecodesign regulation information:

- This product is considered to be a "containing product" in the sense of Regulations (EU) 2019/2020 and (EU) 2019/2015.
- Tolerances of the reported values, are according to LED Modules Performance standard IEC/EN 62717.
- In general, the replacement of the contained light sources without permanent damage to the product with the use of common available tools is possible in the final application when they can be dismantled from the installation environment and substituted for the necessary number of light sources restoring its full electrical/mechanical/thermal/optical functionality by means of a professional installer. In the contrary, and limited to the LINEARlight Flex Diffuse, LINEARlight Rigid Finesse, GINO LED Flex Diffuse and LUMINENT Milky product families, the contained light source is an integrated part of the containing product and its removal can only be done by causing a permanent damage to the containing product due to its tight mechanical, electrical, optical, thermal interaction and/or environmental protection with or from the containing product. Therefore, a replacement of the light source with the use of common available tools is not justified.
- Dismantling of light sources from containing products at end of life: Containing products with light sources which are scalable in length can be cut to the length of the contained light source and if applicable mechanically detached from protective and/or optical covers. Containing products shall be separated from building material and/or from other additional mounting accessories by means of a professional installer. Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

Dati logistici

Codice prodotto	Descrizione del prodotto	Unità di imballo (Pezzi/unità)	Dimensioni (lunghezza x profondità x altezza)	Volume	Peso lordo
4062172106627	TFP300-G1 -827-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106641	TFP300-G1 -830-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106665	TFP300-G1 -840-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106702	TFP300-G1 -865-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106689	TFP300-G1 -850-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106726	TFP1000-G1 -827-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106740	TFP1000-G1 -830-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g

Scheda della famiglia di prodotto

Dati logistici

4062172106764	TFP1000-G1 -840-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106801	TFP1000-G1 -865-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106788	TFP1000-G1 -850-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106825	TFP2000-G1 -827-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g
4062172106849	TFP2000-G1 -830-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g
4062172106863	TFP2000-G1 -840-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g
4062172106900	TFP2000-G1 -865-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g
4062172106887	TFP2000-G1 -850-05	Cartone di spedizione 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g

1)☒ codice prodotto indicato descrive la minore quantità che può essere ordinata. Una unità di spedizione può contenere uno o più di un singolo prodotto. Quando si inserisce un ordine, per la quantità inserire una o più unità di spedizione.

Accessori opzionali

Descrizione del prodotto	Nome dell'accessorio	Codice dell'accessorio
TFP300-G1 -827-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -827-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -827-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -827-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -827-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -827-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -827-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -827-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP300-G1 -830-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -830-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -830-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -830-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -830-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -830-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -830-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -830-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853

Scheda della famiglia di prodotto

TFP300-G1 -840-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -840-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -840-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -840-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -840-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -840-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -840-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -840-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP300-G1 -865-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -865-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -865-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -865-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -865-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -865-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -865-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -865-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP300-G1 -850-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -850-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -850-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -850-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -850-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -850-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -850-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -850-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -827-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -827-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -827-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -827-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -827-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP1000-G1 -827-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP1000-G1 -827-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP1000-G1 -827-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -830-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -830-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -830-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -830-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -830-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP1000-G1 -830-05	FX -SC08-G2-CT4PJ	▶ 4052899464858

Scheda della famiglia di prodotto

TFP1000-G1 -830-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP1000-G1 -830-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -840-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -840-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -840-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -840-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -840-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP1000-G1 -840-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP1000-G1 -840-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP1000-G1 -840-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -865-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -865-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -865-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -865-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -865-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP1000-G1 -865-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP1000-G1 -865-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP1000-G1 -865-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -850-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -850-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -850-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -850-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -850-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP1000-G1 -850-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP1000-G1 -850-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP1000-G1 -850-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -827-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -827-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -827-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP2000-G1 -827-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP2000-G1 -827-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -827-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -827-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -827-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -830-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -830-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -830-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP2000-G1 -830-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988

Scheda della famiglia di prodotto

TFP2000-G1 -830-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -830-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -830-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -830-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -840-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -840-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -840-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP2000-G1 -840-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP2000-G1 -840-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -840-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -840-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -840-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -865-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -865-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -865-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP2000-G1 -865-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP2000-G1 -865-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -865-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -865-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -865-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -850-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -850-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -850-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP2000-G1 -850-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP2000-G1 -850-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -850-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -850-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -850-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853

Clausola

Con riserva di modifiche senza preavviso. Salvo errori o omissioni. Assicurarsi sempre di utilizzare la versione più recente.